

EXE-12C6602A020

C4000 Fusion Ex

SAFETY LIGHT CURTAINS





Ordering information

| Туре | part no. |
|-----------------|----------|
| EXE-12C6602A020 | 1097731 |

Other models and accessories → www.sick.com/C4000_Fusion_Ex

Illustration may differ









Detailed technical data

Features

| Application | Explosive areas |
|-------------------------|---|
| Ex-approvals | ATEX for gas: II 2 G Ex db IIB T6 ATEX for dust: II 2 D Ex tb IIIC T56 °C Db IP6X NFPA 70/NEC 500 Class I, Div. 1, Groups C and D NFPA 70/NEC 500 Class II, Div. 1, Groups E, F and G NFPA 70/NEC 500 Class III, Div. 1 |
| System part | Receiver |
| Resolution | 30 mm |
| Protective field height | 1,200 mm |
| Scanning range | 17.6 m |
| Synchronization | Optical synchronization |

Safety-related parameters

| Туре | Type 4 (IEC 61496-1) |
|---|--|
| Safety integrity level | SIL 3 (IEC 61508) |
| Category | Category 4 (EN ISO 13849) |
| Performance level | PL e (EN ISO 13849) |
| $\ensuremath{PFH_D}$ (mean probability of a dangerous failure per hour) | 15 x 10 ⁻⁹ (EN ISO 13849) |
| T _M (mission time) | 20 years (EN ISO 13849) |
| Safe state in the event of a fault | At least one OSSD is in the OFF state. |

Functions

| | Functions | Delivery status |
|----------------------------------|-----------|-----------------|
| Protective operation | ✓ | |
| Restart interlock | ✓ | External |
| External device monitoring (EDM) | ✓ | Deactivated |

| Beam coding | ✓ | Uncoded |
|---|----------|---------------|
| Configurable scanning range | ✓ | |
| Reduced resolution | ✓ | Deactivated |
| Fixed blanking | ✓ | Deactivated |
| Floating blanking | ✓ | Deactivated |
| Dynamic blanking for object pattern recognition | ✓ | |
| Self-teaching dynamic blanking for goods detection | ✓ | |
| Self-teaching dynamic blanking for pallet detection | ✓ | |
| Multiple sampling | ✓ | 2x evaluation |
| Direction monitoring | ✓ | |
| Virtual photoelectric switches | ✓ | |
| Sensor gap monitoring | ✓ | |
| Sequence monitoring | ✓ | |
| Object entry monitoring | ✓ | |
| Detection of geometrically even objects | ✓ | |
| Safe SICK device communication via EFI | ✓ | |

Functions in combination with UE402

| Bypass | √ |
|--------------------------|----------|
| Operating mode switching | ✓ |

Interfaces

| System connection | Connecting cable (30 m) with flying leads, 12-wire |
|--------------------------|---|
| Cable diameter | 10 mm |
| Conductor cross section | 0.75 mm ² |
| Configuration connection | Female connector M8, 4-pin |
| Configuration method | PC with CDS (Configuration and Diagnostic Software) |
| Display elements | 7-segment display |

Electrical data

| Protection class | III (IEC 61140) |
|---|--|
| Supply voltage V _S | 24 V DC (19.2 V 28.8 V) ¹⁾ |
| Residual ripple | ≤ 10 % ²⁾ |
| Output signal switching devices (OSSDs) | |
| Type of output | 2 PNP semiconductors, short-circuit protected, cross-circuit monitored ³⁾ |
| ON state, switching voltage HIGH | 24 V DC (V _S - 2.25 V DC V _S) |
| OFF state, switching voltage LOW | ≤ 3.5 V DC |
| Current-carrying capacity per OSSD | ≤ 500 mA |

¹⁾ The external voltage supply must be capable of buffering brief mains voltage failures of 20 ms as specified in EN 60204-1. Suitable power supplies are available as accessories from SICK.

 $^{^{2)}}$ Within the limits of $\ensuremath{\text{V}_{\text{S}}}.$

 $^{^{\}rm 3)}$ Applies to the voltage range between –30 V and +30 V.

| Application diagnostic output (ADO) | |
|-------------------------------------|--|
| Type of output | PNP semiconductor, short-circuit protected ³⁾ |
| Output voltage HIGH (active) | 24 V DC (V _S - 4.2 V DC V _S) |
| Output voltage LOW (deactivated) | High resistance |
| Output current HIGH (active) | ≤ 100 mA |

¹⁾ The external voltage supply must be capable of buffering brief mains voltage failures of 20 ms as specified in EN 60204-1. Suitable power supplies are available as accessories from SICK.

Mechanical data

| Dimensions | See dimensional drawing |
|-----------------------|--------------------------|
| Housing cross-section | 161.8 mm x 142.1 mm |
| Housing material | Aluminum cast/AlSi7Mg0.6 |

Ambient data

| Enclosure rating | IP65 (EN 60529) IP66 (EN 60529) |
|-------------------------------|------------------------------------|
| Ambient operating temperature | 0 °C +55 °C |
| Storage temperature | -25 °C +70 °C |
| Air humidity | 15 % 95 %, Non-condensing |
| Vibration resistance | 5 g, 10 Hz 55 Hz (EN 60068-2-6) |
| Shock resistance | 10 g, 16 ms (EN 60068-2-27) |

Other information

Certificates

| EU declaration of conformity | ✓ |
|---|---|
| China-RoHS | ✓ |
| ATEX certificate | ✓ |
| IECEx certificate | ✓ |
| cULus certificate | ✓ |
| Information according to Art. 3 of Data Act (Regulation EU 2023/2854) | ✓ |

Classifications

| ECLASS 5.0 | 27272704 |
|--------------|----------|
| ECLASS 5.1.4 | 27272704 |
| ECLASS 6.0 | 27272704 |
| ECLASS 6.2 | 27272704 |
| ECLASS 7.0 | 27272704 |
| ECLASS 8.0 | 27272704 |
| ECLASS 8.1 | 27272704 |
| ECLASS 9.0 | 27272704 |
| ECLASS 10.0 | 27272704 |

 $^{^{2)}}$ Within the limits of $\mbox{\rm V}_{\mbox{\scriptsize S}}.$

 $^{^{\}rm 3)}$ Applies to the voltage range between –30 V and +30 V.

| ECLASS 11.0 | 27272704 |
|----------------|----------|
| ECLASS 12.0 | 27272704 |
| ETIM 5.0 | EC002549 |
| ETIM 6.0 | EC002549 |
| ETIM 7.0 | EC002549 |
| ETIM 8.0 | EC002549 |
| UNSPSC 16.0901 | 46171620 |

Recommended accessories

Other models and accessories → www.sick.com/C4000_Fusion_Ex

| | Brief description | Туре | part no. | | | |
|--|---|----------------|----------|--|--|--|
| device protection and care | | | | | | |
| SICK | Product family: Cleaning agents Description: Cloth for cleaning optical surfaces | Lens cloth | 4003353 | | | |
| Mounting syst | Mounting systems | | | | | |
| -190% | Description: Alignment bracket for explosion-proof enclosure Packing unit: 2 pieces | BEF-1SHABRST2 | 2072525 | | | |
| connectors and cables | | | | | | |
| | Note: Suitable for deTec4 Core Ex, C4000 Advanced Ex and C4000 Fusion Ex safety light curtains | Cable gland | 5329002 | | | |
| network devices | | | | | | |
| The state of the s | | UE4740-22H0000 | 1046978 | | | |
| Commissioning aids and test equipment | | | | | | |
| | Product: Alignment aids Dimensions (W x H x L): 19 mm 67.3 mm 66.9 mm Description: Laser alignment aid for various sensors, laser class 2 (IEC 60825). Do not look into the beam! | AR60 | 1015741 | | | |
| | Product: Test equipment Description: 30 mm diameter, 250 mm length | Test rod 30 mm | 2022602 | | | |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

